## Oasis 3-Piece, 60 x 32, Ramped Threshold, Roll-In Shower Compartment With ActivLife 2-Bar (2-horizontal) Package




**Specification** – Oasis 3-piece FRP gelcoat shower compartment SH3P-MD-6032, having a ½-inch high maximum finished threshold with floor attachment flange on lower threshold. ActivLife package includes a single horizontal bar on the back wall and the control wall.

## **Standards Certification:**

The shower compartment listed is manufactured in compliance with ANSI Z124 Standards, and certified through an ongoing, independent quality assurance and testing program.

The factory-applied grab bar package is certified through an independent review program.


**NOTE:** This model DOES NOT meet the required interior dimensions for ADA Roll-In Shower compliance.




Model ID	Package Code	Description (define configuration referencing drain end)
SH3P-MD-6032 L (left drain) / BP1-60 SH3P-MD-6032 R (right drain) / BP1-60		60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.50" dia. stainless steel 2-bar package (single horizontal back wall bar, single horizontal bar on control wall).
Powder Coated Bar Packages (1.25-inch dia.)		
SH3P-MD-6032 L (left drain SH3P-MD-6032 R (right dra	,	60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. white powder coated 2-bar package (single horizontal back wall bar, single horizontal bar on control wall).
SH3P-MD-6032 L (left drain SH3P-MD-6032 R (right dra	,	60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. off-white powder coated 2-bar package (single horizontal back wall bar, single horizontal bar on control wall).
SH3P-MD-6032 L (left drain SH3P-MD-6032 R (right dra	,	60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. nickel finish 2-bar package (single horizontal back wall bar, single horizontal bar on control wall).
	ADD / SHWR ROD-SH	Factory installed 1" dia. stainless steel shower curtain rod.

## Package Notes:

- 1. Model available without listed package.
- 2. For 3-bar package, adding a vertical bar on control wall, see ActivLife "BP2-60" package code.
- 3. For bar and seat packages, see ActivLife "TL-RS/LS" and "TLV-RS/LS" package codes.
- 4. For REINFORCEMENT ONLY replicating "TL" package with RH or LH seat reinforcement, see ActivLife "TLRF-RS" or "TLRF-LS" package code.
- 5. For REINFORCEMENT ONLY for horizontal bars (HUD/FHA-Fair Housing), see ActivLife "FH" package code.
- 6. For expanded reinforcement package options, (with or without listed package components), see ActivLife "3SM" and "3SF" package codes.









- Photo 1: Grab Bars: Factory-installed 1.50-inch diameter, concealed attachment, 18 gauge, #304 brushed stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)
- Photo 2: Grab Bars: Factory-installed 1.25-inch dia. powder coated (in finishes listed above), concealed attachment, 18 gauge, #304 stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)