## Oasis 3-Piece, 60 x 32 ABF Configured Bathtub With (ICC/ANSI A117.1-2009) 4-Horizontal Bars, 1-Vertical Bar And Pivot-Hinge FOLDING Seat Package




**Specification** – Oasis 3-piece, 60 x 32-inch deep, FRP gelcoat bathtub model TS3P-6032 ABF (<u>17.25-inch apron</u>) having a factory-equipped package in compliance with ICC/ANSI A 117.1-2009. Package includes 2-horizontal bars on back wall, single horizontal bar on head end wall, horizontal bar on control wall, vertical bar at entry on control wall, pivot-hinge <u>FOLDING in-tub seat</u> at head end and shower curtain rod.

## Standards Certification:

The bathtub listed is manufactured in compliance with ANSI Z124 Standards, and certified through an ongoing, independent quality assurance and testing program.

The factory-applied grab bars and seat package are installed in compliance with ICC / ANSI A117.1 Standards, and certified through an independent review program.



Dimensions shown are maximum. Due to the nature of the materials involved, actual unit dimensions can vary (tolerances: +0 / -3/8 inch). Oasis reserves the right to modify or discontinue product and/or associated equipment without prior written or verbal notification or obligation


## Model IDPackage CodeDescription (define configuration referencing drain end)TS3P-6032 LABF / ANS09-FLD60" x 32", end drain, multi-piece tub-shower, with 17.25" apron, 5-bars (dual horizontal back<br/>wall bars, single horizontal bar on each end wall, single vertical bar on control wall) with<br/>white phenolic folding seat and shower curtain rod.


DELETE / SHWR ROD-TS

Delete shower curtain rod from ANS09 package. (DOES NOT compromise package compliance).

## Package Notes:

- 1. Model available without listed package.
- 2. For 5-bar and removable seat package, see "ANS09-REM" package code.
- 3. For 4 bars (less vertical bar) and seat package, see "ADA10" package code.
- 4. For 2, 3, 4, and 5-bar packages without a seat, see ActivLife "BP1-60", BP2-60", "4BAR", and "5BAR" package codes.
- 5. For REINFORCEMENT ONLY for bars (based on ANS09 package less seat), see ActivLife "FH" package code.
- 6. For expanded reinforcement package options, (with or without listed package components), see ActivLife "3SM" and "3SF" package codes.





- Photo 1: Grab Bars: Factory-installed 1.50-inch diameter, concealed attachment, 18 gauge, #304 brushed stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)
- Photo 2: FOLDING In-Tub Seat: Factory-installed seat with non-porous, high-pressure laminate upper and lower surfaces, fused to high-density phenolic core. The seat area secures to an 18 gauge, #304 stainless steel framework, and easily pivots upward to store along the wall without supplemental fasteners. Heavy-duty wall (hinge) bracket design eliminates supplemental legs and is formed from 10 gauge, #304 brushed stainless steel. (Reinforced area includes a structural core material encapsulated in FRP composite.)
- Photo 3: Shower Curtain Rod: Factory-installed 1.00-inch diameter, concealed attachment, 18 gauge, stainless steel shower curtain rod with polished finished.